



COMEN

Central Monitoring Solution

Powerful website funtion to provide you with comprehensive intermnet connection solution. You can get access to patients' information more convenient.



STAR8000F

Multi-parameters Monitor



Shenzhen Comen Medical Instruments Co., Ltd.

Hotline: 400 700 9488

Add: Floor 7, Block 5, 4th Industrial Park of Nanyou, Nanshan District, Shenzhen City 518052, China
 Tel: +86-755-2641 7452 2643 1473 2643 1236 Fax: +86-755-2643 1232 Website: en.comen.com E-mail: service@szcomen.com

All rights reserved by Comen, specifications are subject to change without notice.

STAR8000F


Multi-parameters Monitor

Functions and performances

- 12.1" LED backlight touch screen with low power consumption and longer battery life.
Support mouse, keyboard operation (optional), and the operation is more humane.
- Fan-less design, ultra quiet.
- Comen patent blood pressure interface, more convenient to plug.
- Support external laser printer with A4 paper reports; support alarm trigger print function.



Large capacity storage, support data save function.

The interface is simple and intuitive and can be dynamically layout as users' preference. Support system software upgrading without disassemble of the machine.



The ASIC chip, more comprehensive care

In the hardware configuration, we use ADI company's integrated analog front-end (ASIC) chip instead of the traditional components, which is designed particularly for monitoring and diagnostic ECG measurement.




Multiple Working Modes

- Standby mode
- Privacy mode
- Night mode
- Extracorporeal circulation mode

NIBP Assisted Vein Puncture

Nurses can use NIBP inflatable cuff to produce pressure close to diastolic pressure to assist vein puncture.




Full screen interface

Make it more convenient for the doctors to observe the specified ECG real-time waveform in a long time.



Other Bed Observation Interface

It is able to observe other monitor's clinical data of the same internet without central station.



Modular design of the plates

- Star8000F adopts modular structure between each plates inner the machine, which eliminates wire connection between module and the side panel, largely reducing wires consumption and prevent disorder situation inner the machine.
- With modular design, star8000F is more stable with higher anti-interference capability so as to improve transportation safety and effectiveness.